

## Gamma Wipe® 67

Sterile Polyester / Cellulose Nonwoven Wiper

Gamma Wipe®67 is a polyester / cellulose blend wiper recommended for ISO Class 5 and above environments composed of 45% polyester and 55% cellulose. Each package is gamma irradiated to a 10<sup>-6</sup> Sterility Assurance. This combination of properties provides Gamma Wipe®67 with the level of cleanliness, abrasion resistance and chemical compatibility required for cleaning general sterile processing areas where both economy and cleanliness are required



### Key Attributes

- 55% cellulose / 45% polyester hydroentangled nonwoven
- No secondary binders
- Available in two sizes: 9x9" and 12x12"
- Gamma irradiated and sterile validated to a 10<sup>-6</sup> Sterility Assurance Level per AAMI guidelines
- Header style packaging with Package Integrity testing
- Lot number on each pack
- Certificate of Sterility with each case and available on the web by lot number 24/7. Details: Expiration Date, Radiation Dosage, Lot Information, Meets cGMP requirements for traceability

### Benefits

- Excellent combination of the synthetic polyester strength and cleanliness with the absorbent characteristics of cellulose.
- Smooth, highly absorbent and durable with low extractable levels
- Economical
- Chemically compatible with common cleaning and disinfecting solutions including isopropyl alcohol, phenols, bleaches and quarternary ammonium compounds

### Applications

- Designed for use in ISO Class 5 and higher sterile environments and USP <797> applications
- Designed for cleaning sterile surfaces and equipment during aseptic processing
- General wiping in component prep, compounding and wash areas
- General wipedowns in sterile gowning rooms
- Applying and removing cleaning and disinfecting solutions

### Other Sterile wipers

- Gamma Wipe SuperSorb®
- Gamma Wipe® 300
- Gamma Wipe® 120

### Pre-Wetted Option

The same wiper material can be provided in pre-wetted formats for reduced VOC emissions, increased convenience, increased productivity, improved solvent control and cleaning protocol repeatability and reduced costs. Pre-wetted options include WFI.

### Validated Sterile

ANSI/AAMI/ISO procedures have been followed for verification of irradiation dose with audits being performed to monitor bioburden levels and dose. The Sterility Assurance Level (SAL) or the probability of a viable organism being present on a product unit after sterilization is a SAL of 10<sup>-6</sup> (which is the chance of 1 non-sterile unit in 1,000,000).

[www.berkshire.com](http://www.berkshire.com)

Contact: Tel 1 800 242 7000 / 1 413 528 2602  
info@berkshire.com

America	Tel 1 413 528 2602	info@berkshire.com
Europe	Tel + 44 1953 562800	enquiries@berkshire.uk.com
SE Asia	Tel 65 6252 4313	enquiries@berkshire.com.sg
Japan	Tel 81 3 4530 9883	master@berkshire.co.jp

## Technical Data:

Attribute		Units	Value	Test Method
Basis Weight		g/m <sup>2</sup>	68.0	TAPPI T-410
Caliper		µm	264	TAPPI T-411
Fibers	≥100µm	fibers/cm <sup>2</sup>	160	IENT-RP-CC004.4 Sec 7.1.3/Sec 7.2.2 modified
Particles	≥0.5µm	x10 <sup>3</sup> /cm <sup>2</sup>	10	IENT-RP-CC004.4 Sec 7.1.3/Sec 7.2.1 modified
Sorbency	Capacity	mL/m <sup>2</sup>	320	IENT-RP-CC004.4 Sec 9.1 / Sec 9.2 modified
	Efficiency	mL/g	4.7	
	Rate	seconds	2	
Non-Volatile Residue	DI Water	g/m <sup>2</sup>	0.028	IENT-RP-CC004.4 Sec 8.1.2
	IPA	g/m <sup>2</sup>	0.0038	
Ions	Na <sup>+</sup>	ppm	62	IENT-RP-CC004.4 Sec 8.2.2
	K <sup>+</sup>	ppm	5.9	
	Ca <sup>++</sup>	ppm	22	
	Mg <sup>++</sup>	ppm	5.0	
	Cl <sup>-</sup>	ppm	31	

### Notes:

- Technical data represented in this table are typical values at the time of publication. These should not be used as product specifications.
- Due to differences in test methods applied and equipment utilized by different wiper manufacturers, valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions
- Third party testing can be performed upon request

## Order Information:

Product	Number	Size	Shts/pk	Pks/Inner bag	Inner bags/cs	Pks/cs	Style
Gamma Wipe® 67	GW67ST0980	9x9"(23x23cm)	20	5	16	80	Header Bag
Gamma Wipe® 67	GW67ST1242	12x12"(30x30cm)	25	7	6	42	Header Bag
Gamma Wipe® 67	GW67ST25	12x12"(30x30cm)	20	5	5	25	Header Bag
Gamma Wipe® 67	GW67ST60	12x12"(30x30cm)	5	10	6	60	Header Bag

## Other Berkshire Products



Wipers



Mop Systems




Face Masks



Glove Liners



Documentation Systems



Swabs